

W: 740 mm L: 645 mm H: 770 mm









The NS Plus is an entry level electrospinning machine, designed to accommodate the maximum components required for an optimized and versatile

Electrospinning Process. It's an ideal solution for lower-budget projects working on small-scale nanofibers research.

It has 3 Hybrid Nozzles, spinning on a rotating drum collector or plate collector, therefore enabling the production of both well-aligned and randomly collected nanofibers. The homogeneity system allows the user to produce a uniform and homogeneous nanofibers membranes.

NSPLUS

| Description | Entry Level Multi Nozzle |
|---------------|--------------------------|
| | Electrospinning Unit |
| Spinning-Type | Side By Side Spinning |
| opining-1/pc | Side by Side Spiriting |

CONSTRUCTION

Dimensions

| Chasis | Closed Chassis For Spinning Area (Included in NS 1 Plus) |
|-----------------------|--|
| Feeding Area Material | PE 1000 (High Density, Chemical resistant) |
| Collector Material | 7000 Series Aluminum Alloy, Stainless Steel |
| LED Illumination | |
| Exhaust Fan | |
| Total Weight | Approx. 60 kgs |
| | |

HIGH VOLTAGE POWER SUPPLY

| Voltage Range | 0- 30 kV |
|-------------------|----------|
| Voltage Precision | 0,1 kV |
| Max. Current | 0.170 mA |

HIGH PRECISION MICRO PUMP

| Flow Rate | 0.35 - 7123 ml/h (BD 60 ml syringe) |
|---------------------|-------------------------------------|
| Flow Rate Precision | 0.01 ml/h |
| Available Syringes | All types are available |



FEEDING AREA

| Number of Nozzles | 3 |
|---|---|
| Feeding Pipe Material | Aluminium |
| Nozzle Material | Electrically Conductive Stainless Steel |
| Nozzle Inner Diameter | 0.8 mm |
| Compatible with Standard Syringe Nozzles | |
| Minimum Required Solution for Single Nozzle Feeding | 2 ml |

| ROTATING COLLECTOR | |
|--------------------------------------|---|
| Drum Collector | |
| Material | Aluminum |
| Dimensions of Drum (D x L) | 100mm x 220 mm |
| Fiber Deposition Area | 314 mm x 220 mm |
| Drum Rotating Speed | 100-500 RPM (Able to produce aligned nanofibers.) |
| Surface Speed (cm/s) | 52,3 cm/s - 261,6 cm/s |
| Stroke of Coating Homogeneity System | Adjustable Between 30 mm and 80 mm |
| Speed of Coating Homogeneity System | Adjustable Between 2 mm and 20 mm/sec |

SPINNING DISTANCE

| Distance Between Nozzle and Collector | 30 mm-230 mm |
|---------------------------------------|----------------|
| Distance Adjustment | Manual Control |

STATIONARY PLATE COLLECTOR

| Material | Stainless Steel |
|-------------------------------|-----------------|
| Distance Adjustment Precision | 275mm x 150mm |

UNIQUE USER INTERFACE

Saving & recalling all parameters via recipe & recall function

| 4,3" Touch screen control panel with well designed user friendly interface | |
|--|--|
| Fully able to control all parameters | |

SAFETY FUNCTION

| SAFETT FONCTION | |
|--|--|
| Emergency Button & Safety Relay | |
| HV Warning Light | |
| Electrical Isolated & Grounded Cabinet | |
| Over Current Protection | |